



MARQUE

Vision Comes to Life

Non Priced 4721



Exp. Date: 12/31/2011
 Quote No: 10020-0006
 Job/Order No: 4721
 AMBULANCE: MA-1-148CO Type I Model 148 Commando

07/29/2013

Page 1

PART NO	S	DESCRIPTION	QTY	ID
		== Type I Model 148 Commando - 1.000 09/20/11 ==	1	SJC
00-00-0020		Order Coordinator - Michele Yoder - (574) 970 6774	1	SJC
		AMBULANCE CONVERSION	1	SJC
03-35-0110		2012 Conversion, Type I, Model 148 Commando	1	SJC
04-20-0400	S	/-- Conversion, Type I, Headroom, 72"	1	SJC
04-20-2400		/-- Conversion, Type I, Body Width, 93" (Standard)	1	SJC
04-20-4030		/-- Conversion, Type I, Body Length, 150" ILO 148"	1	SJC
04-10-1000	>	/-- Change to Standard Dimensions (Per Inch)	2	SJC
		CHASSIS	1	SJC
05-20-0710	S	> Chassis, 2012 Dodge Ram 4500HD, 4x2 168.5" WB, Diesel	1	SJC
06-00-0410		> /-- Running Boards, One (1) Pair ADP (Type I)	1	SJC
06-00-0710	< >	/-- Grip Strut Inserts in Running Boards IATS	1	SJC
		Align strut section to run parallel with the outer edge of the running board - no top side welds		
12-55-0110		/-- Mudflaps, Front, Included with Running Boards	1	SJC
06-20-0100		/-- OEM Mirrors STD	1	SJC
06-50-0720	< >	/-- Suspension, Rear Air Ride, Link Electrical Dodge	1	SJC
		Wire a magnetic switch so that system dumps with the left rear entry door - reinflates when closed - replace the manual drain valve and lanyard with a Velvac auto-drain valve		
		8M000100 - Unit for Dodge 4500		
		800M1074 - Electronic Control Panel		
		800M1200 - Kit Commercial Electric		
		800M1072 - Electronic Sensor Kit		
		13010559 - Heated Drain Valve		
06-50-1000		/-- Suspension, Rear Air Ride, Installed Prior to Body Mounting	1	SJC
06-50-1110	< >	/-- Suspension, Rear Air Ride, Dump Override Switch IATS	1	SJC
		On/Off style switch - in "on" position allows the air ride to kneel when the left rear entry door is open. In the "off" position, prevents the suspension from kneeling. Install at the rear door		
90-14-0110	<	/-- Air Ride Suspension Safety Sign (Standard)	1	SJC
		Installed in the cab per Engineering Bulletin #044		
		"WARNING - Driving this vehicle without air in the rear suspension could cause loss of vehicle control and/or damage to the suspension."		

PART NO	S	DESCRIPTION	QTY	ID
		2" x 4" White lettering on red background		
06-60-0200		<i>/-- Rubberized Vinyl Cab Flooring STD</i>	1	SJC
06-70-0100	<	<i>/-- Spare Tire, Shipped Loose</i> Deletes the mounting bolt, nut and plate	1	SJC
06-70-4030		<i>/-- Wheel Sims - Phoenix 19.5", Set of Four (4) Dodge</i> Phoenix ND1907 (116691)	1	SJC
06-80-0130	< >	<i>/-- Air Fill Extensions, Rear Tires (19.5"), Phoenix "Air Max"</i> installed per the manufacturer's instructions Phoenix #AMH1	1	SJC
36-10-0300		<i>/-- Cab/Chassis Lighting Package, Dodge 4500 RAM</i>	1	SJC
37-15-0510	<	<i>/-- Warn. Light, Grille, Pass. Side, Whel LED Warn. Dodge 4500, Cast</i> SHIPPED LOOSE. INSTALLED IN DEALER INSTALLED BRUSH GUARD	1	SJC
49-04-1210	S	<i>/-- Warning Light, Whelen,500 series</i>	1	SJC
49-20-2015	S	<i>/-- Whelen,500,Red,LED Flashing, Clear Lens,w/o flange</i> 70R02FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-3600		<i>/-- Grille Bezel, Cast, Dodge, Pass. Side</i> Cast LH37632-1 (115207)	1	SJC
50-00-8200		<i>/-- Deutsch water proof connector</i>	1	SJC
37-25-0510	<	<i>/-- Warn. Light, Grille, Driver Side, Whel LED Warn. Dodge 4500, Cast</i> SHIPPED LOOSE. INSTALLED IN DEALER INSTALLED BRUSH GUARD	1	SJC
49-04-1210	S	<i>/-- Warning Light, Whelen, 500 series</i>	1	SJC
49-20-2015	S	<i>/-- Whelen,500,Red,LED Flashing, Clear Lens,w/o flange</i> 70R02FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-3610		<i>/-- Grille Bezel, Cast, Dodge, Driver Side</i> Cast LH37633-1 (115208)	1	SJC
50-00-8200		<i>/-- Deutsch water proof connector</i>	1	SJC
37-35-1010		<i>/-- Warn. Light, Inters., Pass. Side, Whel LED Warn. Dodge 4500, Cast</i>	1	SJC
49-20-2015		<i>/-- Whelen,3x7,Red,LED Flashing, Clear Lens,w/o flange</i> 70R02FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-4080		<i>/-- Intersection Bezel, Cast, Dodge, Pass. Side</i> Cast LH37760 (116809)	1	SJC
50-00-8200		<i>/-- Deutsch water proof connector</i>	1	SJC
37-45-1010		<i>/-- Warn. Light, Inters., Driver Side, Whel LED Warn. Dodge 4500, Cast</i>	1	SJC
49-20-2015		<i>/-- Whelen,3x7,Red,LED Flashing, Clear Lens,w/o flange</i> 70R02FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-4090		<i>/-- Intersection Bezel, Cast, Dodge, Driver Side</i> Cast LH37761 (116808)	1	SJC
50-00-8200		<i>/-- Deutsch water proof connector</i>	1	SJC
55-18-0210	<	<i>/-- Siren Speakers, Dodge 4500</i> Ship loose Installed at dealer location siren speaker	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
		116810 116811		
57-16-0110	<	/-- Auxiliary AC Condensor, Pro Air Skirt Mount On Type III units, this option requires a 9.5" deep side entry step ILO 12.5" Includes mudflaps before and after Wire to operate whenever both cab and module A/C system is on	1	SJC
57-00-0500	<	/-- Heat / AC Skirt Mount Condenser Kit Install a mud flap forward and rearward of the condenser. Pro Air 106 (50 000 590) (SJC 3481)	1	SJC
57-18-0100	<	/-- Booster Pump - 12V Install in the water supply line to the heater Pro Air #05 000 295 (113580)	1	SJC
69-06-0500	<	/-- Console, Cab, MultiSpec Aluminum Dual Cup Holders	1	SJC
69-10-2040		/-- Multispec Color: Greystone MS99-6072 MS99-6072	1	SJC
		CHASSIS COMPONENTS AND ACCESSORIES	1	SJC
06-50-2000		Front End Alignment, Chassis Pre-Delivery w/Printed Report	1	SJC
		MODULE CONSTRUCTION	1	SJC
08-10-0100		Roof Construction, 4"x4" formed channel @ 16" o.c. (Standard)	1	SJC
08-20-0140		Wall Construction, 2x2's @ 12" o.c. (Type I)	1	SJC
08-30-0300	S <	Crawl-Thru, Type I, Extended Cab Roof w/ Hinged Door Crawl-thru ILOS - bellows mount w/extended cab roof - includes hinged walk-thru bulkhead door w/ fixed Plexi vision panel	1	SJC
08-50-0100		Floor Construction, (Standard)	1	SJC
08-60-0100		Body-to-Chassis Mounting, Type I (Standard)	1	SJC
		UNDERCOATING AND INSULATION	1	SJC
10-00-0110	<	Undercoating, Module Floor, Ziebart ILOS applied to underside of module only - after unit is off-line - this option deletes the standard Dolphin undercoating Ziebart	1	SJC
10-10-0300		Insulation, Walls and Ceiling, Spray Foam	1	SJC
10-10-0410		Insulation, Entry Doors, Spray Foam Yoder Insulation	1	SJC
10-10-0510	<	Insulation Enhancement, Temp-Coat Ceramic Spray IATS 30 mil coating - spray inside roof, walls, backside of compartment cans, inside entry doors (before plank foam is installed), top side of the subfloor before any flooring material is installed.	1	SJC
10-10-0720	<	Insulation, Floor, Spray Foam Cover bottom side of floor w/ .060" aluminum - seal any gaps	1	SJC
		EXTERIOR BODY TRIM and ACCESSORIES	1	SJC
12-05-0100	<	Drip Rail Trim Mouldings Over Door Openings (Standard) Mouldings to extend no more than 1/4" beyond each side of the door openings	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
12-10-0100	<	Stone Guards, ADP, Front Wall (Standard) ADP installed on the lower portions of the front wall, outboard of the chassis - see prints	2	SJC
12-20-0100		Rub Rails, Skirt Line, One (1) Set ADP	1	SJC
12-30-0110		Fenderettes, One (1) Pair Stainless Steel Thomas Hardware: Type III - #TH4026 Type I w/ 215/16 tires - #TH4026 Type I w/ 235/16 or 225/19.5 tires - #TH4024 Type I w/ LT225/19.5 or 245/19.5 tires - #TH4028	1	SJC
12-35-0100		Fuel Fill Bezel, Cast Aluminum (Standard) Cast Products #FG2101-1-250 (Ford / Chevy Type I) (107231) #FG5301-1-250 (Ford / Chevy Type III) (107397)	1	SJC
12-40-0200		Rear Bumper, Grip Strut Folds-Up Into Pocket In Rear Riser	1	SJC
12-45-0100		Rear Riser, ADP (Standard)	1	SJC
12-50-0100	<	License Plate Bracket, Recessed (Standard) When mounting bracket, please put ECK on all mounting screws. Mount on the lower left corner Cast Products #LP0002-1	1	SJC
50-00-8100		-- License Plate Light, LED Optronics UCL-11CKB	1	SJC
12-55-0500	<	Mudflaps, Rear, One (1) Pair Rubber, w/Logo w/ Marque Logo Dura Guard #26205925R	1	SJC
		COMPARTMENT CONSTRUCTION and COMPONENTS	1	SJC
14-15-0100	<	Streetside-Front Compartment (#1), ADP, 1" Dished Floor (Std.) ADP - 1" dished floor Add cut out and removable panel to forward wall of compartment. Attach with 10x24 rev-nuts. Place foam tape behind panel to prevent rattling.	1	SJC
14-20-0100	<	Streetside #2 Compartment, ADP, Sweep Out (Std.) .125" ADP, sweep-out floor	1	SJC
69-36-0100	<	-- CPR Seat w/ Hinged Backrest and Seat (STD) Includes lap style seat belt	1	SJC
14-35-0100	< >	Streetside-Rear Compartment (#4), ADP, 2" Dished Floor (Type I Std.) .125" ADP - 2" dished floor	1	SJC
14-45-0110	< >	Curbside-Rear Compartment (#5), ADP, 4" Dished Floor (Std.) .125" ADP - 4" dished floor	1	SJC
14-60-0120	<	Side Entry Stepwell, Type I, ADP (Standard) Tube support welded in with audioguard sprayed over it.	1	SJC
14-65-0100		ALS Compartment Door (#8)	1	SJC
15-10-0490		Vertical Divider, Delete Standard from SS#1	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
15-10-0820	< >	Protective Coating for Divider(s), Two Sides IATS Gray color	1	SJC
15-10-1000	<	Adjustable Shelf in SS#2 (Standard) .125" smooth aluminum, includes four shelf brackets and black pinch trim installed on the outside edge of the shelf	1	SJC
15-10-1110	< >	Adjustable Shelf IATS Shelf/shelves to be full depth (2" less than the depth of the compartment). (1). ss2 (3) ss4	4	SJC
15-10-1210		Compartment Adjustable Shelf Tracks, Unistrut Thomas-Austin: Channel: 107204 Channel nuts: 107250	1	SJC
15-10-1410	< >	Protective Coating for Compartment Shelf IATS coat the inside surfaces of the shelf and the outer facing vertical edges	1	SJC
15-10-1800	< >	Plastic Tiles on Compartment / Shelf Floors Includes Mate flex matting on all compartments, shelves, and trays Mateflex Versaflex -	1	SJC
15-10-1840	< >	/-- Plastic Tile Color - Gray ILO Black Grey tiles Mateflex Versaflex	1	SJC
MODULE DOOR CONSTRUCTION and COMPONENTS			1	SJC
16-10-0100		Extruded/Pan Formed Hybrid Doors (Standard)	1	SJC
16-10-0300		/-- Electrical Feed to All Doors - Curly Cord	1	SJC
16-20-0100		Compartment and Entry Door Latching Hardware (Standard) Compartment doors in excess of 23" tall shall receive dual nadir pins	1	SJC
16-20-0130		Compartment Door Handles, Eberhard	5	SJC
16-00-0600		/-- Eberhard, Chrome Exterior Locking SJC 115519 handle SJC 11537/73 rotary latch SJC 119081/j-20 brass door rod connector to prevent door rattle (TH2989)	5	SJC
16-22-0120		Curbside Entry Door	1	SJC
16-22-1100		/-- Curbside Entry Door Handles, Eberhard	1	SJC
16-00-0600		/-- Eberhard, Chrome Exterior Locking SJC 115519 handle SJC 11537/73 rotary latch SJC 119081/j-20 brass door rod connector to prevent door rattle (TH2989)	1	SJC
16-00-0610		/-- Eberhard, Interior Locking SJC 115370	1	SJC
16-22-2000		/-- Curbside Entry Door Closer - Gas Strut	1	SJC
16-24-0120		Rear Entry Doors	1	SJC
16-24-1100		/-- Rear Entry Door Handles, Eberhard	1	SJC
16-00-0600		/-- Eberhard, Chrome Exterior Locking SJC 115519 handle SJC 11537/73 rotary latch SJC 119081/j-20 brass door rod connector to prevent door rattle (TH2989)	1	SJC
16-00-0610		/-- Eberhard, Interior Locking SJC 115370	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
16-00-0620		<i>/-- Eberhard, Interior Non-Locking</i> SJC 115371	1	SJC
16-24-3000		-- Rear Entry Doors, Cast Grabber Door Checks (Standard) Cast Products DH0017	1	SJC
16-24-3610	<	<i>/-- Emergency Exit Latches Required</i> INCLUDES RED WITH WHITE LETTER LABEL (EMERGENCY EXIT LATCH)	2	SJC
WINDOWS				
16-30-0100	<	Window, Side Entry Door, Upper, Dark Tint black frame	1	SJC
16-35-0010		-- Window, 19" X 18" Dark Tint Slider Clear Vision Windows: 9FM500026	1	SJC
16-35-0200		-- Clamp Ring - Window 19" X 18" - 2.28" Wall Clear Vision Windows: 9PCR00001	1	SJC
16-30-0600	<	Window, Rear Entry Door, Upper, Dark Tint black frame	2	SJC
16-35-0030		-- Window, 19" X 18" Dark Tint Fixed Clear Vision Windows: 9FMI00051	2	SJC
16-35-0200		-- Clamp Ring - Window 19" X 18" - 2.28" Wall Clear Vision Windows: 9PCR00001	2	SJC
16-35-0070		<i>Window, 36" X 18" Dark Tint Slider</i> Clear Vision Windows: 9FM500020	1	SJC
16-35-0220		<i>/-- Clamp Ring - Window 36" X 18" 2.28" Wall</i> Clear Vision Windows: 9PCR00120	1	SJC
REFLECTORS				
16-40-0120	<	1" x 4" Reflector - Red (standard) installed on the lower rear of the streetside and curbside walls just above the rubrail and in the right corners of the rear wall just above the rear riser. Grote 40132-3	4	SJC
16-40-0510		Compartment Door Reflectors	5	SJC
16-40-0140	<	-- 3" round reflector - Red Install 3" round reflectors Optronics RE13RB (115491)	5	SJC
MISCELLANEOUS BODY COMPONENTS				
ELECTRICAL FEATURES and COMPONENTS				
12 VOLT POWER COMPONENTS				
31-10-0120		12 Volt Load Center Location [J-Box] (Standard)	1	SJC
31-10-0200	<	<i>12 Volt Electrical System, FirstTronics</i> INSTALL REAR SWITCH PANEL ON THE CURBSIDE, ANGLED.	1	SJC
31-00-0100		-- 12 Volt Electrical System, FirstTronics 107358,59,60 - Communication Cables 107346 - Front Panel 107348 - Rear Panel 107421 - Power Distribution 107347 - Electronic Control Board	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
31-10-0350	< >	-- Warning Light Sequencer System FirstTronics Sequencer to operate on load start-up only 107349	1	SJC
31-15-0195	<	-- Driver's Control Console Gauges FirstTronics incorporated in the front switch panel	1	SJC
53-12-0105		 -- Warning Light Flasher, Vanner 5860GCPE (Standard) 5860GCPE (117140)	1	SJC
53-16-0100		-- Warning Light Flash Pattern, K-Spec	1	SJC
31-10-0510	< >	Power Locks for Module Entry Doors Includes actuator, actuator connector, actuator pigtail, relay connector - one switch installed on CS wall just inside the side entry door, one switch installed on the rear wall just inside the CS rear entry door Includes tie in to OEM cab chassis doors (including Key faubs if chassis is so equipped)	1	SJC
31-10-0530	< >	Power Locks for Compartment Doors Includes actuator, actuator connector, actuator pigtail, relay connector - Use same switch as entry doors	6	SJC
31-10-0610	>	 -- Relay for Compartment Door Power Locks	6	SJC
31-10-0560	< >	Remote Power Switch to Activate Cab & Module Door Locks install in license plate Cole Hersee 55065-03 Switch and Cole Hersee rubber boot 81264	1	SJC
31-20-0120	<	Module Power Disconnect Switch, TST Remote mounted in the J-box and wired to operate with the ignition switch w/ 5 minute delay unless indicated otherwise. Must include a 5 minute timer. TST CDR-357	1	SJC
31-20-0300	< >	Battery Charger/Converter, Pre-Wire (Type I) Includes a power and ground lead terminated in the SS#2 compartment - if inverter w/ battery charger is also specified, route wiring to the location specified in the inverter option	1	SJC
32-26-0400	< >	 -- Inverter, Vanner 1050W w/ 55A Battery Charger wired to power interior receipts install in the ceiling next to the vac pump. Cover is an ADP cover. 20-1050 CUL DC (SJC#116842)	1	SJC
31-20-0320		 -- Battery charger is included in selected inverter	1	SJC
31-25-0100	<	12 Volt Recepts, Cigarette Lighter Style, Two(2) (1) in the Action Area, (1) in the ALS cabinet unless specified otherwise	1	SJC
31-00-0400		-- 12 Volt Recepts, Cigarette Lighter Style SJC #115351	2	SJC
31-25-0380		Clock, DELETE Standard Trin-Tec	1	SJC
		110/220 VOLT WIRING AND COMPONENTS	1	SJC
32-10-0100	<	110 Volt AC Wiring And Components Electrical system - 120-Volt	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
32-14-0300	<	Shoreline, 20A Straight Blade, Levitron Includes a 20amp circuit breaker. THIS SHORELINE IS FOR THE OUTLETS	1	SJC
32-00-0200		-- Shoreline Inlet, 20A Straight Blade - Levitron Levitron 15378CWP (113825)	1	SJC
32-18-0110	>	-- Shoreline, Delay/Interrupter, Kussmaul Dynamic Disconnect Kussmaul Dynamic Disconnect 091-18-098	1	SJC
32-14-0700	< >	Shoreline, 20A Kussmaul "Super Auto-Eject" THIS SHORELINE IS FOR THE HEATER	1	SJC
		Inlet, Cover and Connector: Kussmaul Electronics 091-55-20-120 Interrupter: Internal (107636)		
32-26-0110	>	Inverter, Pre-Wire (Standard)	1	SJC
32-26-0115		Refer to Part #31-20-xxxx for Specific Inverter Information	1	SJC
32-30-0100	<	Recepts, 110V AC Hospital Grade Duplexes (1) in Action Area, (1) in Defib. area, (1) in ALS cabinet	1	SJC
32-00-0100		-- Recepts, Interior 110V AC Hospital Grade Duplex Recept: Wesco 8200HLI (115776) Box-Recessed Wesco 9301E (105476) Flush (105534) Cover Wesco SS8 (105510)	3	SJC
32-30-0210	< >	/-- Recept, 110V AC Hospital Grade Duplex, Interior IATS on the curbside by the side entry door.	1	SJC
32-00-0100		/-- Recepts, Interior 110V AC Hospital Grade Duplex Recept: Wesco 8200HLI (115776) Box-Recessed Wesco 9301E (105476) Flush (105534) Cover Wesco SS8 (105510)	1	SJC
		INTERIOR LIGHTING and COMPONENTS		
33-10-0100		Dome lights, Dual Filament Incandescent, Eight (8)	1	SJC
33-00-0110		/-- Dome lights, Dual Filament Incandescent, Weldon Weldon 8040-0520-080 w/1157 bulb (106012)	8	SJC
16-50-0110		-- Backer Plates for Dome llights For 12" tube spacing - DLC012"OC For 16" tube spacing - DLC016"OC	8	SJC
33-10-0191	<	Dome Lights, Streetside Activate on Opening of Entry Doors Streetside dome lights shall automatically light on their "low" setting when the rear entry doors or the side entry door is opened.	1	SJC
33-10-0370	< >	Timer, 60 Minute w/o Hold Feature installed in the curbside wall adjacent to the side entry door - see prints	1	SJC
		dome lights Wesco FF60M (106773)		
33-10-0430	< >	Cabinet Lighting, Surface Mount LED One light per cabinet space installed on the backside of the cabinet face - just above the door opening to shine toward back of cabinet - any exposed wiring to be installed in plastic raceway fastened in the upper corners of the cabinet as necessary. Includes light in 2nd A/A.	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
		Lights: Maxxima #LED-300CL Raceway: Outwater Plastics Hide-a-Cord self adhesive cover #1300-WH w/13002IE-WH inside corners - or similar		
33-10-0670	<	Light, Side Entry Stepwell, (1) Whelen OS Surface Mount LED install on the right (front) wall of the stepwell	1	SJC
50-00-7250		/-- Whelen OS series 45 deg. - Clear 0AC0EDCR (117332) Steady Burn	1	SJC
33-10-0730	< >	Entry Door LED Warning Lights - Whelen OS Series Installed at bottom of entry doors - see prints - lights are to flash whenever the module entry doors are open and battery power is enabled. If this is not a multiplex system, it will also require a wigwag flasher and three (3) 4-prongs relays. Add magnetic switch to left entry door leaf.	1	SJC
50-00-7220		/-- Whelen OS series, Flashing - RED OSR00FCR (115803) Flashing	3	SJC
33-10-0800	<	Action Area Light, Liteco 8" Slimline Incandescent wired to switch in AA switch panel Liteco #18543936 (115752)	1	SJC
33-10-1010	<	Spotlight, Handheld, Optronics "BlueEye", 400,000 CP (Std.) Hard wired under the cab console Fasten wire with PClamp at rear of seat base. Optronics KB4003 (108555)	1	SJC
33-10-2010		ALS Cabinet Lights, Rectagular Surface Mount Dual Bulb Incandescent	2	SJC
53-30-0180		/-- Rectagular Dual Bulb Incandescent w/Clear Lens Vans 1211W (106550)	2	SJC
		EXTERIOR LIGHTING and COMPONENTS		
34-10-0400	<	Exterior Lighting Requirements - General All light fixtures to be installed using nylon inserts unless directed otherwise. On secondary mode; grille, intersection, and center clear warning lights drop off.	1 1	SJC SJC
		DOT LIGHTING		
34-25-0100		/-- DOT Clearance and Marker Lighting	1	SJC
34-25-0300		/-- DOT Clearance and Marker Lighting (Upper Perimeter Module Walls) - STD	1	SJC
50-00-7000		/-- DOT Clearance and Marker Lighting RED MCL13RB	7	SJC
50-00-7010		/-- DOT Clearance and Marker Lighting AMBER MCL13AB	7	SJC
34-25-0210	<	/-- Corner Lights Feature , (4) Lower Module Corners Use Micro Plastics round head Nylon inserts for these lights.	1	SJC
12-10-0210		/-- Corner Guards, Four (4) ADP w/ Corner Light Cutouts	4	SJC
34-25-0340		/-- Corner Lights - STD	1	SJC
50-00-7000		/-- DOT Clearance and Marker Lighting RED MCL13RB	6	SJC

PART NO	S	DESCRIPTION	QTY	ID
50-00-7010		<i>/-- DOT Clearance and Marker Lighting AMBER</i> MCL13AB	6	SJC
50-00-6000		<i>/-- Corner Light Bezel</i> Cast LH14702-4	4	SJC
		FRONT MODULE WALL EXTERIOR LIGHTING	1	SJC
35-12-0165		<i>/-- Lightbar, Front, None Required, 7-Light Pattern, Whel LED Warn. w/f</i>	1	SJC
35-90-0400		<i>/-- Lightbar, Front, None Required</i>	1	SJC
43-10-0165		<i>/-- Warn. Light, Front Passenger Side #1, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen,7x9,Red,LED Flashing, Clear Lens,w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
43-12-0165		<i>/-- Warn. Light, Front Passenger Side #2, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen,7x9,Red,LED Flashing, Clear Lens,w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
43-14-0165		<i>/-- Warn. Light, Front Passenger Side #3, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen,7x9,Red,LED Flashing, Clear Lens,w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
43-15-0165		<i>/-- Warn. Light, Front Center, Whel LED w/f</i>	1	SJC
49-24-2230		<i>/-- Whelen,7x9,Clear,LED Flashing, Clear Lens,w/ flange</i> 90CC5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC	1	SJC
43-17-0165		<i>/-- Warn. Light, Front Driver Side #3, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen,7x9,Red,LED Flashing, Clear Lens,w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
43-19-0165		<i>/-- Warn. Light, Front Driver Side #2, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen,7x9,Red,LED Flashing, Clear Lens,w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
43-20-0165		<i>/-- Warn. Light, Front Driver Side #1, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen,7x9,Red,LED Flashing, Clear Lens,w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
49-22-3220		<i>/-- Whelen,4X6,Amber,Turn LED,w/ flange</i> 60A00TAR	2	SJC
50-00-1020		<i>/-- Whelen, 4x6 Chrome Flange</i> 6EFLANGE	2	SJC
50-00-8200		<i>/-- Deutsch water proof connector</i> REAR MODULE WALL EXTERIOR LIGHTING	2	SJC
38-41-0615		<i>/-- Lightbar, Rear, None Required, Whel LED Warn. w/f</i>	1	SJC
45-10-0165		<i>/-- Warn. Light, Rear Passenger Side, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen,7x9,Red,LED Flashing, Clear Lens,w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
45-12-0615		<i>/-- Scene Light, Rear Passenger Side, Whel LED w/f</i>	1	SJC
49-24-5665		<i>/-- Whelen,7x9,Clear 24 Diode LED,Scene,w/ flange</i> 9SC0ENZR - Super-LED 24 Diode Light	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC	1	SJC
45-15-0165		<i>/-- Warn. Light, Rear Center, Whel LED w/f</i>	1	SJC
49-24-2225		<i>/-- Whelen,7x9,Amber,LED Flashing, Clear Lens,w/ flange</i> 90AA5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
45-17-0615		<i>/-- Scene Light, Rear Driver Side, Whel LED w/f</i>	1	SJC
49-24-5665		<i>/-- Whelen,7x9,Clear 24 Diode LED,Scene,w/ flange</i> 9SC0ENZR - Super-LED 24 Diode Light	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC	1	SJC
45-20-0165		<i>/-- Warn. Light, Rear Driver Side, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen, 7x9, Red, LED Flashing, Clear Lens, w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
49-24-2210	<	<i>/-- Whelen, 7x9, Red, LED Flashing, Color Lens, w/ flange</i> To show through the rear windows 90RR5FRR (115190) - Flashing/Programmable with Color lens	4	SJC
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only 90FLANGC (115265)	4	SJC
38-89-9410		<i>/-- Rear Scene Lights, Activate on Opening of Rear Entry Doors</i>	1	SJC
38-89-9510		<i>/-- Rear Scene Lights, Activate on Reverse Gear</i>	1	SJC
		STOP, TAIL, TURN, AND BACKUP LIGHTING	1	SJC
45-35-0515	<	<i>/-- T/B/T/BU Lights, Whelen, 4x6, LED, single turns, w/f</i> Includes one (1) pair of brake/tail lights, one (1) pair of turn signals, and one (1) pair of back-up lights mounted on the rear exterior module wall.	1	SJC
49-22-3220		<i>/-- Whelen, 4X6, Amber, Turn LED, w/ flange</i> 60A00TAR	2	SJC
50-00-1020		<i>/-- Whelen, 4x6 Chrome Flange</i> 6EFLANGE	2	SJC
50-00-8200		<i>/-- Deutsch water proof connector</i>	2	SJC
49-22-4210		<i>/-- Whelen, 4X6, Red, Brake/Tail LED, w/ flange</i> 60R00XRR - Maximum Intensity	2	SJC
50-00-1020		<i>/-- Whelen, 4x6 Chrome Flange</i> 6EFLANGE	2	SJC
50-00-8200		<i>/-- Deutsch water proof connector</i>	2	SJC
49-22-5230		<i>/-- Whelen, 4X6, Clear, Backup LED Min, w/ flange</i> 60C00VCR - Minimum Intensity	2	SJC
50-00-1020		<i>/-- Whelen, 4x6 Chrome Flange</i> 6EFLANGE	2	SJC
50-00-8200		<i>/-- Deutsch water proof connector</i>	2	SJC
		CURBSIDE MODULE WALL EXTERIOR LIGHTING	1	SJC
47-10-0165		<i>/-- Warn. Light, CS Front, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen, 7x9, Red, LED Flashing, Clear Lens, w/ flange</i> 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
50-00-1070	<	/-- Whelen, 7x9 Chrome Flange for Super-LED This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
47-20-0615		/-- Scene Light, CS Front, Whel LED w/f	1	SJC
49-24-5665		/-- Whelen, 7x9, Clear 24 Diode LED, Scene, w/ flange 9SC0ENZR - Super-LED 24 Diode Light	1	SJC
50-00-1070	<	/-- Whelen, 7x9 Chrome Flange for Super-LED This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
47-30-0615		/-- Scene Light, CS Rear, Whel LED w/f	1	SJC
49-24-5665		/-- Whelen, 7x9, Clear 24 Diode LED, Scene, w/ flange 9SC0ENZR - Super-LED 24 Diode Light	1	SJC
50-00-1070	<	/-- Whelen, 7x9 Chrome Flange for Super-LED This flange is for the Super-LED model only 90FLANGC	1	SJC
47-40-0165		/-- Warn. Light, CS Rear, Whel LED w/f	1	SJC
49-24-2215		/-- Whelen, 7x9, Red, LED Flashing, Clear Lens, w/ flange 90RR5FCR - Flashing/Programmable with Clear lens	1	SJC
50-00-1070	<	/-- Whelen, 7x9 Chrome Flange for Super-LED This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
47-40-9410		/-- CS Scene Lights, Activate on Opening of Entry Door STREETSIDE MODULE WALL EXTERIOR LIGHTING	1	SJC
47-60-0165		/-- Warn. Light, SS Front, Whel LED w/f	1	SJC
49-24-2210		/-- Whelen, 7x9, Red, LED Flashing, Color Lens, w/ flange 90RR5FRR (115190) - Flashing/Programmable with Color lens	1	SJC
50-00-1070	<	/-- Whelen, 7x9 Chrome Flange for Super-LED This flange is for the Super-LED model only 90FLANGC (115265)	1	SJC
47-70-0615		/-- Scene Light, SS Front, Whel LED w/f	1	SJC
49-24-5665		/-- Whelen, 7x9, Clear 24 Diode LED, Scene, w/ flange 9SC0ENZR - Super-LED 24 Diode Light	1	SJC
50-00-1070	<	/-- Whelen, 7x9 Chrome Flange for Super-LED This flange is for the Super-LED model only 90FLANGC	1	SJC
47-80-0615		/-- Scene Light, SS Rear, Whel LED w/f	1	SJC
49-24-5665		/-- Whelen, 7x9, Clear 24 Diode LED, Scene, w/ flange 9SC0ENZR - Super-LED 24 Diode Light	1	SJC
50-00-1070	<	/-- Whelen, 7x9 Chrome Flange for Super-LED This flange is for the Super-LED model only	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
		90FLANGC (115265)		
47-90-0165		<i>/-- Warn. Light, SS Rear, Whel LED w/f</i>	1	SJC
49-24-2215		<i>/-- Whelen,7x9,Red,LED Flashing, Clear Lens,w/ flange</i>	1	SJC
		90RR5FCR - Flashing/Programmable with Clear lens		
50-00-1070	<	<i>/-- Whelen, 7x9 Chrome Flange for Super-LED</i> This flange is for the Super-LED model only	1	SJC
		90FLANGC (115265)		
47-90-9400		<i>/-- SS Scene Lights, Do NOT Activate on Opening of SS Compartment Doors</i>	1	SJC
47-90-9500		<i>/-- Side Wall Scene Lights, Do Not Activate on Reverse Gear</i>	1	SJC
		ARROW LIGHTBARS	1	SJC
		WARNING LIGHT and HEADLIGHT FLASHERS	1	SJC
		STROBE POWER SUPPLIES	1	SJC
		AUXILIARY LIGHTING	1	SJC
53-34-0130	< >	Compartment Lights, 4" Recessed LED one (1) per compartment - if installed below the floor line, seal backside of flange w/ foam tape two (2) in SS#2	9	SJC
53-30-0130		<i>/-- 4" Recessed 10 diode LED</i> Optronics BUL11CBX Clear 10 diode (118588)	9	SJC
		AUDIBLE WARNING DEVICES	1	SJC
55-00-0010		Refer to Chassis Section Above for Correct Siren Speakers	1	SJC
55-10-0100		Back-up Alarm, 97 dBa (Standard) EC520 (115164)	1	SJC
55-12-0220		Siren, Whelen 295HFSA7 295HFSA7 (115350)	1	SJC
		COMMUNICATION PROVISIONS AND EQUIPMENT	1	SJC
55-34-0100	>	Antenna Base, Coax, Power and Ground Wires (Standard)	1	SJC
55-00-0100	<	<i>/-- Antenna Base, Coax, Power and Ground Wires</i> RG58U coax with 10 ga. power and ground wires - label the base and coax end ANT#1 - terminate in the front console Hutton - Maxrad K-794 (if 17' req'd.) - or - Maxrad KE-794 (if 30' req'd.)	1	SJC
55-00-0120		<i>/-- Antenna Coax</i>	1	SJC
55-00-0130		<i>/-- Antenna Power and Ground</i>	1	SJC
55-00-0140		<i>/-- Antenna Base</i> Hutton - Maxrad K-794 (if 17' req'd.) - or - Maxrad KE-794 (if 30' req'd.)	1	SJC
55-00-0200		<i>/-- Breaker, 20 AMP</i>	1	SJC
55-36-0110	>	Antenna Base, Coax(es), Power and Ground Wires IATS	1	SJC
55-00-0100	<	<i>/-- Antenna Base, Coax, Power and Ground Wires</i> RG58U coax with 10 ga. power and ground wires - label the base and coax end ANT#2 - terminate in the action area Hutton - Maxrad K-794 (if 17' req'd.) - or - Maxrad KE-794 (if 30' req'd.)	1	SJC
55-00-0120		<i>/-- Antenna Coax</i>	1	SJC
55-00-0130		<i>/-- Antenna Power and Ground</i>	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
55-00-0140		-- Antenna Base Hutton - Maxrad K-794 (if 17' req'd.) - or - Maxrad KE-794 (if 30' req'd.)	1	SJC
55-00-0200		-- Breaker, 20 AMP	1	SJC
55-38-0110	<	Radio Power and Ground Wires IATS 10 ga. power (red) and ground (black) wired to a 50A breaker in the J-box - terminated behind the passenger seat	1	SJC
55-00-0130		-- Antenna Power and Ground	1	SJC
55-00-0200		-- Breaker, 20 AMP	1	SJC
		ENVIRONMENTAL SYSTEMS AND COMPONENTS	1	SJC
57-10-0110	<	Heat / AC, Pro Air Ducted Combo System NOTE: before installing the ducts, spray or roll Temp Coat to the bottom side of the roof metal between the center hat section and the first "Z" rails to serve as a thermal break	1	SJC
10-10-0550	<	-- Insulation Enhancement, Temp-Coat Ceramic Spray Ducted A/C 30 mil coating - spray on area of roof where Heat-A/C ducting will be run	1	SJC
57-00-0210		-- Heat / AC Pro Air #935 12v Ducted Combo System HEAT/AC: Pro Air 935 w/ top discharge Pro Air #50 000 920	1	SJC
57-00-0300	<	-- Heat / AC Water Valve, Manual On Type I Chassis please mount manual valve and electric/vacuum valve inside A/C -Heat cabinet. Not under vehicle. On Type III chassis, mount manual valves behind removable panel in streetside #1. Mount electric/vacuum valve in A/C cabinet. Pro Air 800307 (105858) Manual	2	SJC
57-00-0310		-- Heat / AC Water Valve, Electric Pro Air 63-000-180 (109869) Electric	1	SJC
57-00-0400		-- Heat / AC Duct Adapters SJC 118759 (2) SJC 118758 (3)	8	SJC
57-00-0410		-- Heat / AC Ducted Vents Pro Air 11-000-135	8	SJC
57-00-0420		-- Heat / AC Ducted Vent Retainers Pro Air 11-000-052	8	SJC
57-00-0425		-- Heat / AC Ducted Vent Adapter ACC #14563400A	8	SJC
57-00-0430		-- Heat / AC Rigid Ducting 118755 118756	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
57-00-0435		-- Heat / AC Flexible Ducting SJC 105854	1	SJC
57-00-0440		-- Heat / AC Plenum SJC 118757	1	SJC
57-00-0460		-- Heat / AC Face Plate Prodesign 3092233	1	SJC
57-00-0470		 -- Heat / AC Pad Larry's Upholstery	1	SJC
57-12-0100		-- Heat / AC System Installed Above Walk/Pass-Thru	1	SJC
57-14-0130	< >	Auxiliary Heater, Broan 750/1500W, 120V Installed at the foot of the bench	1	SJC
		SHELTER: #174		
57-20-0100		Thermostat, Pro Air (Standard) Pro Air 01000203 (108063)	1	SJC
57-24-0110		Exhaust Fans, Dual 12V Blowers (Standard)	1	SJC
57-00-0100		-- Exhaust Fans, 12V Blower Detmar 751 (106333)	2	SJC
57-00-0110		 -- Cowl Vent - 4" Polished Attwood #1364A1 (115345)	2	SJC
57-00-0120		-- Rectagular Vent - 8"x4" Polished Cast VC00011 (105578)	1	SJC
		INTERIOR FEATURES and COMPONENTS	1	SJC
		ENTRY DOOR FINISHES and COMPONENTS	1	SJC
60-10-0100		Entry Doors Liners, 2-Piece Split Design	1	SJC
60-10-0260	<	 -- Entry Doors, Upper Liners, Aluminum w/ Multispec Face Attach using six (6) stainless or black oxide screws w/ finish washers	1	SJC
69-10-2040		 -- Multispec Color: Greystone MS99-6072 MS99-6072	1	SJC
60-10-0500		-- Entry Doors, Kick Plates, ADP (Standard)	1	SJC
62-10-0100		Entry Door Grab Bars, 1.25" x 12" S/S Straight Bar Marson G304116521 (116521)	3	SJC
		CEILING GRAB BARS	1	SJC
62-30-0030	<	Grab Bar, Above Cot, 1.25" x 96" Stainless Steel (STD) all fastening points must fall on roof tubes or backer plates - See print	1	SJC
		UPHOLSTERY	1	SJC
68-10-0010	< >	Upholstery, Seamless Vinyl, Solid Color (Standard) solid color seamless	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
68-10-0200		<i>/-- Upholstery Color, Gunmetal</i>	1	SJC
68-10-0520	<	Padded Vinyl Trim (Standard) Vertical and horizontal edges above the monitor/defib and action area	1	SJC
		FLOOR COVERING	1	SJC
68-20-0120	>	<i>Flooring, Lon Seal "Lon Coin II Flecks", SWB</i>	1	SJC
68-20-0700		<i>/-- Flooring Color, "Lon Coin II Flecks", Moonstone #157</i> SILL, SCUFF and COT WHEEL PLATES	1	SJC
68-30-0100		<i>Floor Sill Plates, Brushed Stainless Steel (Standard)</i> #4 polished 20 Gauge stainless steel	1	SJC
		ATTENDANT'S SEAT	1	SJC
69-08-0200		<i>Attendant's Seat, Wise Child Safety Seamless</i> Wise # WM1615 (118829)	1	SJC
69-08-1100		<i>/-- Attendant's Seat Base, Wise Swivel</i> SJC #116670	1	SJC
		CABINETY PACKAGES	1	SJC
69-10-0140	< >	<i>Interior Cabinetry, Alum. Structure Commando</i> Includes aluminum structure, aluminum cabinet inserts, Sintra cabinet doors, aluminum shelves and aluminum backed facing materials	1	SJC
69-10-2000		<i>/-- -- Select Multispec Color for Cabinet Face (REQUIRED)</i>	1	SJC
		CEILING FINISHING	1	SJC
69-12-0410	<	<i>/-- Headliner, Patient Compartment, Aluminum</i> .090 smooth w/ White	1	SJC
		ELECTRICAL (J-BOX) CONSTRUCTION	1	SJC
69-14-0100		<i>/-- Electrical (J-Box) - Standard Configuration</i>	1	SJC
		ALS CABINET	1	SJC
69-16-0100		<i>/-- ALS Cabinet - Standard Configuration</i>	1	SJC
69-18-0110	<	<i>/-- Glove Box Cabinet, Three Hole Design Above Side Entry</i> Use 3/8" thick Plexi - see prints Use stainless steel position hinge - 3 per window Hinge from McMaster Carr #1460A1 / SJC #112785	1	SJC
		SQUAD BENCH and COMPONENTS	1	SJC
69-22-0120	S <	<i>/-- High-Back seat inlu of squad bench</i> IncludesSPECIAL - Install a WM-1932 Wise high back vacuum formed seat w/3 Point seat Belt at head of squad bench. Seat will be capable of swiveling 360 degrees and will lock out in 45 degrees so that all attendants can face forward. Base is a WM-1931. This seat has the capability of adding the passenger awareness system.	1	SJC
69-22-0900	S	<i>/-- No Floor Cove, Riser see Prints</i>	1	SJC
69-22-1120	S	<i>/-- No Squad Bench Lid, Single, Aluminum See Prints</i>	1	SJC
69-22-1220	S	<i>/-- No Squad Bench Interior, Aluminum Insert See Prints</i>	1	SJC
69-22-1410	S < >	<i>/-- No Embossed Rubber Liner Under Squad Bench - Delete</i> install on floor of storage space under squad bench - adhere rubber w/ Chemrex adhesive Alert Mfg	1	SJC
		STREETSIDE CABINETY	1	SJC
69-30-0110	< >	<i>/-- Streetside Cabinety - Custom Configuration</i> The Streetside shall be configured to allow for a secondary litter when the CPR seat is folded down. See prints. Add backers for the seatbelts.	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
		CPR SEAT	1	SJC
69-36-0010		/-- Refer to Part #14-25-xxxx for CPR Seat Construction Info.	1	SJC
69-36-0170		/-- CPR Seat Interior, Aluminum Insert	1	SJC
69-36-0190	< >	/-- Embossed Rubber Liner Under CPR Seat installed on floor of storage space only - adhere rubber w/ Chemrex adhesive Alert Mfg.	1	SJC
		ACTION / MONITOR-DEFIB. AREA COMPONENTS	1	SJC
69-40-0120	< >	/-- Countertop, Action Area, Solid Surface Material Build cabinets with flat counter tops (no lips) - bottom screws in back wall to be lowered and sunk flush so they are hidden by the solid surface top - color to match the action area counter	1	SJC
69-40-0610		/-- Solid Surface Countertop Color - Dusk	1	SJC
69-40-0220	< >	/-- Countertop, Monitor/Defib, Solid Surface Material Build cabinets with flat counter tops (no lips) - bottom screws in back wall to be lowered and sunk flush so they are hidden by the solid surface top - color to match the action area counter	2	SJC
69-46-0110	< >	/-- Inside Access to Exterior Compartment IATS See prints for location(s) Curbside Rear Compartment at inside/outside access must be full depth. Full length dual plexiglas doors.	1	SJC
		SHELVES and SHELVING COMPONENTS	1	SJC
69-48-0130	<	/-- Cabinet Shelves, .125" Aluminum .125" smooth w/ painted finish, 3/4" bend up at front and down at rear edge - glue embossed rubber to shelf floor	1	SJC
69-48-0430	< >	/-- Cabinet Shelf Track, Unistrut Aluminum Upgrades all interior cabinet shelf tracks - including ALS cabinet Thomas-Austin Channel: #TB9111 Channel nuts: #TB9050	1	SJC
		DIVIDERS	1	SJC
		CABINET DOORS/WINDOWS and DRAWERS	1	SJC
69-52-0120	<	/-- Cabinet Doors/Windows, General (Sintra) See prints. All Sliding Plexiglas Doors to have stops placed in window track. 10mm white Korylte (Parkland Plastics) w/ .090 powder coated smooth aluminum facing - satin edge trim	1	SJC
69-58-0115		/-- Plexiglas Color, Clear	1	SJC
69-60-0100	< >	/-- Door/Drawer Latch, Southco Flush Pull see prints	1	SJC
		MEDICAL SYSTEMS and COMPONENTS	1	SJC
		OXYGEN SYSTEM and EQUIPMENT	1	SJC
71-14-0100		On-Board Oxygen Cylinder Bracket, "M" Size (Standard)	1	SJC
71-00-1800		/-- On-Board Cylinder Base, "M" Size 115713	1	SJC
71-00-1810		/-- On-Board Cylinder Bracket, "M" Size 115712	2	SJC

PART NO	S	DESCRIPTION	QTY	ID
71-00-1840		-- 17" equipment strap 115755	1	SJC
71-00-1850		-- Footman's Loop 3" 105473	2	SJC
71-16-0100		Oxygen Cylinder Wrench (Standard) SJC #105888	1	SJC
71-20-0100	< >	Oxygen Outlets, Ohio Style Quick Disconnect (2 in Action Area) (1) in Action Area (1) in the ceiling in the wire chase above the head of the cot	1	SJC
71-00-1400		-- Oxygen Outlets, Ohio Style Quick Disconnect	2	SJC
71-00-1010		-- Oxygen / Vacuum / Medical Air Trim Bezel Part of complete assembly	2	SJC
		MEDICAL AIR SYSTEM and EQUIPMENT	1	SJC
		VACUUM SYSTEM and EQUIPMENT	1	SJC
71-50-0100		Vacuum System, On-Board w/Ohio Style Outlet	1	SJC
71-52-0100		-- Vacuum Outlet, (1) Ohio Style in Action Area	1	SJC
71-00-1600		-- Vacuum Outlet, Ohio Style	1	SJC
71-00-1010		-- Oxygen / Vacuum / Medical Air Trim Bezel Part of complete assembly	1	SJC
71-54-0110	<	 -- Vacuum Pump, Gast (Standard Types I and III) Installed in SS#2 w/ aluminum wire mesh guard unless specified otherwise	1	SJC
71-00-1550		-- Vacuum Pump, Gast #22D11801011066 (112927)	1	SJC
71-56-0100	<	 -- Vacuum, Aspirator, RICO RS4X Disposable INSTALLED BELOW ACTION AREA IN RECESS. ADP COVER IN SS2 Rico 1001B (106315)	1	SJC
		IV SYSTEM and EQUIPMENT	1	SJC
73-10-0100		IV Hangers, Cast Products Recessed in Ceiling	1	SJC
71-00-0100		-- IV Hangers, Cast Products Recessed in Ceiling Cast Products #IV2008-1 (113850)	2	SJC
16-50-0130		-- Backer Plates for Recessed IV Hangers	2	SJC
		BIO-WASTE CONTAINERS	1	SJC
		COT AND STRETCHER EQUIPMENT	1	SJC
		PRIMARY COTS	1	SJC
		COT FASTENERS	1	SJC
79-14-0110		 -- Cot Fastener, Ferno-Washington 175-3 Single Position (105724)	1	SJC
79-16-0170		 -- Cot Mounts, Set for FW Model 35 - Center	1	SJC
79-18-0130	<	 -- Cot Safety Catch, Ferno-Wash., Installed (Standard - Center) Yellow safety catch installed centered in rear door opening, position "_" from the rear door sill - see Engineering Bulletin #019 for fastening guidelines Emsar 0901308 (106512)	1	SJC
		STRETCHERS and EQUIPMENT	1	SJC
		DECALS and LETTERING	1	SJC
		K-SPEC LETTERING	1	SJC
80-10-0110	< >	Decals, K-Spec Lettering (Shipped Loose) Blue reflective w/ white reflective border - lettering shipped loose:	1	SJC

PART NO	S	DESCRIPTION	QTY	ID
		(1) 4" mirror image AMBULANCE (3) 6" AMBULANCE		
80-00-0100		-- AMBULANCE 6" Decal 105777	3	SJC
80-00-0110		-- ECNALUBMA 4" Decal 105775	1	SJC
		STAR-OF-LIFE DECALS	1	SJC
80-12-0140		Decals, Star-of-Life Package, Delete All	1	SJC
		CUSTOM DECALS	1	SJC
80-18-0500	<	Decals, "Marque" Logo Install... one on each fender, one on passenger rear - lower area one in Action Area one on curbside wall by side entry door	1	SJC
		CUSTOM LETTERING	1	SJC
		DECAL STRIPING	1	SJC
		PAINT	1	SJC
		MODULE PAINT	1	SJC
84-15-1000	<	Paint, Module, PPG - White (Standard) Wheels remain OEM color	1	SJC
		CHASSIS PAINT	1	SJC
		PAINT STRIPING	1	SJC
		MISCELLANEOUS EQUIPMENT and COMPONENTS	1	SJC
90-10-0100	<	Stretcher Strap, Exterior Compartment (Standard) Installed in SS-rear compartment unless directed otherwise - nylon web strap w/ seat belt clip/buckle and two (2) footmans loops	1	SJC
90-14-0100	<	Interior Safety Signs (Standard) Two (2) NO SMOKING-OXYGEN EQUIPPED and two (2) FASTEN SEAT BELTS signs, one (1) each in the cab and in the patient compartment, 110V for each 110V outlet, cleaning sticker in Action Area, "Authorized Service Only" sticker in J Box.	1	SJC
90-22-0100		Owner's Manual / Equipment Packet / OEM Manual	1	SJC
90-24-0100		Fuel Surcharge	1	SJC