



Reliable Emergency Vehicles, Inc
1-800-460-VALU

Quote No: 10007-0001 2013 Type 2 Chevy G3500 155"
AMBULANCE: 2-TYPE2 Type II

02/04/2013

Page 1

DESCRIPTION
== Type II - 1.000 01/03/13 ==
AMBULANCE CONVERSION
Conversion, Type II
CHASSIS
Chassis, 2013 Chevy G3500 Van, 155" WB, Gas
CHASSIS COMPONENTS AND ACCESSORIES
Secondary Chevy Alternator 145 Amp Required
OEM Mirrors STD
Front End Alignment, Chassis Pre-Delivery w/Printed Report
Rubberized Vinyl Cab Flooring STD
Spare Tire, Installed Under Chassis
Roof Construction, Type II
Pass-Thru, Type II, w/ Sliding Plexi Window
UNDERCOATING and INSULATION
Undercoating, Underside of Module Floor (Standard)
Insulation, Walls and Ceiling, R11 Fiberglass Batt (Type II)
EXTERIOR BODY TRIM and ACCESSORIES
Rear Bumper Assembly, Type II
COMPARTMENT CONSTRUCTION and COMPONENTS
WINDOWS
ELECTRICAL FEATURES and COMPONENTS

DESCRIPTION

12 Volt Electrical System, RC Tronics
 12 Volt Recepts, Cigarette Lighter Style

12 VOLT POWER COMPONENTS

Idle Control, Electronic Throttle
 12 Volt Load Center Location [J-Box] (Type II)
 12 Volt Electrical System, RC Tronics with Fuses (Standard)
 No Module Power Disconnect Switch Required
 Battery, Delco Group 78 600 CCA - Installed Under Hood STD
 12 Volt Recepts, Cigarette Lighter Style, Two(2)

110/220 VOLT WIRING AND COMPONENTS

Recepts, Interior 110V AC Hospital Grade Duplex
 Shoreline Inlet, 20A Straight Blade - Levitron
 110 Volt AC Wiring And Components
 Shoreline, 20A Straight Blade, Levitron
 Inverter, Pre-Wire (Standard)
 Refer to Part #31-20-xxxx for Specific Inverter Information
 Recepts, 110V AC Hospital Grade Duplexes (Type II)

INTERIOR LIGHTING and COMPONENTS

Dome lights, Dual Filament Incandescent
 Dome lights, Dual Filament Incandescent, Eight (8)
 Dome Lights, Activate on Opening of Entry Doors
 Light, Side Entry Stepwell, (1) Recessed 3/4" 2 diode LED
 Action Area Light, Arrow Safety, Flanged Surface Mount
 Spotlight, Handheld, Optronics "BlueEye", 400,000 CP (Std.)
 Spotlight Mounting Location (Required)
 Spotlight Mounting Location, Hardwire under passanger seat

EXTERIOR LIGHTING and COMPONENTS**FRONT MODULE WALL EXTERIOR LIGHTING**

Lightbar, Front, None Required, Whel Hal Warn.

Lightbar, Front, None Required
 Cab/Chassis Lighting Package, Chevy G3500
 Warn. Light, Grille, Pass. Side, Whel LED Warn. Chevy G, Cast
 Warn. Light, Grille, Driver Side, Whel LED Warn. Chevy G, Cast
 Warn. Light, Inters., Pass Side, Whel 3x7 LED Warn. w/f
 Warn. Light, Inters., Driver Side, Whel 3x7 LED Warn. w/f

REAR MODULE WALL EXTERIOR LIGHTING

Lightbar, Rear, None Required, Whel Hal Warn.
 Rear Scene Lights, Activate on Opening of Rear Entry Doors
 Rear Scene Lights, Do NOT Activate on Reverse Gear

Warn. Light, Front Passenger Side #1, Whel Hal

DESCRIPTION**WARNING LIGHT and HEADLIGHT FLASHERS**

I-Warning Light Flasher, Vanner 9860GCPE (Standard))
Warning Light Flash Pattern, K-Spec

STROBE POWER SUPPLIES**AUXILIARY LIGHTING**

3/4" Recessed 2 diode LED

AUDIBLE WARNING DEVICES

Refer to Chassis Section Above for Correct Siren Speakers
Back-up Alarm, 97 dBa (Standard)
Siren, Whelen 295HFSA7

Siren Speakers, Chevy G-Series

COMMUNICATION PROVISIONS AND EQUIPMENT

Antenna, Coax

ENVIRONMENTAL SYSTEMS AND COMPONENTS

Exhaust Fans, 12V Blower
Cowl Vent - 4" Polished
Heat / AC Pro Air #935 12v Combo System
Heat / AC Water Valve, Manual
Heat / AC Water Valve, Vacuum
Heat / AC Face Plate
Heat / AC, Pro Air 12V Combo System-Type II
Heat / AC System Installed Above Walk/Pass-Thru
Thermostat, Pro Air (Standard)
Exhaust Fans, Single 12V Blower (Standard)

INTERIOR FEATURES and COMPONENTS**ENTRY DOOR FINISHES and COMPONENTS**

Entry Doors, Liners, OEM (Type II Standard)
Entry Door Grab Handle, Chrome

CEILING GRAB BARS

Grab Bar, Centered, 1" x 72" Stainless Steel (Std.)

UPHOLSTERY

Upholstery, Seamless Vinyl, Solid Color (Standard)
-- Select Vinyl Color (REQUIRED) --

FLOOR COVERING

DESCRIPTION

Flooring, Lon Seal "Lon Coin II Flecks", SWB
 -- Select Flooring Color (REQUIRED) --

SILL, SCUFF and COT WHEEL PLATES

ABS Console - Chevy Gas
 Console, Cab, Chevy Floor Mount, Gas

ATTENDANT'S SEAT

Attendant's Seat, EVS 1782 Seamless 6 Degree Back w/3PT
 Attendant's Seat Base, EVS CBR Box Style

CABINERY PACKAGES

Interior Cabinetry, Fiberglass Type II
 -- Select Fiberglass Color (REQUIRED)

CEILING FINISHING

Headliner, Patient Compartment, Fiberglass

ELECTRICAL (J-BOX) CONSTRUCTION

Electrical (J-Box) - Standard Configuration

ALS CABINET

ALS Cabinet - Standard Configuration

SQUAD BENCH and COMPONENTS

Squad Bench Base, Fiberglass w/ 16" Board Storage
 Floor Cove, 3" Roll Up at Squad Bench Riser
 Squad Bench Lid, Split , 3/4" Plywood
 Embossed Rubber Liner Under Squad Bench
 Pull-Out Drawer at Head of Squad Bench

O2 CABINET

O2 Cabinet - Curbside Rear

STREETSIDE CABINERY

Streetside Cabinetry - Standard Configuration

ACTION / MONITOR-DEFIB. AREA COMPONENTS

Countertop, Action Area, Fiberglass

SHELVES and SHELVING COMPONENTS

Cabinet Shelves, Sintra

DESCRIPTION

Cabinet Shelf Track, Unistrut Aluminum

CABINET DOORS/WINDOWS and DRAWERSCabinet Doors/Windows, General
Plexiglas Color, Clear

Door/Drawer Latch, Southco Flush Pull

MEDICAL SYSTEMS and COMPONENTSIV Hangers, Cast Products Recessed in Ceiling
Trash Container, 2 Gallon
Sharps Container, Straight Drop Style, 4-Quart
Oxygen Outlets, Ohio Style Quick Disconnect
Vacuum Pump, Gast**OXYGEN SYSTEM and EQUIPMENT**Oxygen System - General
On-Board Oxygen Cylinder Bracket, Type II
Oxygen Cylinder Wrench (Standard)
Oxygen Outlets, Ohio Style Quick Disconnect (2 in Action Area)**VACUUM SYSTEM and EQUIPMENT**Vacuum Pump, Gast (Standard Type II)
Vacuum, Aspirator, RICO RS4X Disposable**IV SYSTEM and EQUIPMENT**

IV Hangers, Cast Products Recessed in Ceiling

BIO-WASTE CONTAINERSSharps Container, Straight Drop Style, 4-Quart, Installed
Trash Container, 2 Gallon, Installed**COT AND STRETCHER EQUIPMENT****PRIMARY COTS****COT FASTENERS**Cot Fastener, Ferno-Washington 175-5 Single Position
---Specify Cot Mount Location Based on Cot Chosen**STRETCHERS and EQUIPMENT****DECALS and LETTERING**

