

DEALER: Reliable Emergency Vehicles
 303 Industrial Blvd
 Comanche, Texas 76442

CUSTOMER: Demo

Sales Rep: _____ Terms: _____
 Penalty: _____

| QTY | S | DESCRIPTION |
|-----|-----|---|
| 1 | < | == Type III Model 164 Commando - 9.600 |
| 1 | | CHASSIS |
| 1 | S < | Chassis, 2010 Ford E-450SD Cutaway, 158" WB Diesel |
| 1 | > | Ford Chassis Standard Warranty - 3 Years/36,000 Miles |
| 6 | S > | Conversion, Type III, Headroom, 74" LO 68" |
| 1 | | Conversion, Type III, Body Width, 96" (Standard) |
| 1 | | Conversion, Type III, Body Length, 164" (Standard) |
| 1 | | CHASSIS COMPONENTS AND ACCESSORIES |
| 1 | | OEM Supplied - Lug Wrench |
| 1 | < > | Running Boards, One (1) Pair ADP (Type III) |
| 1 | < > | Grip Strut Inserts in Running Boards IATS |
| 1 | > | Mirrors, Sail Mount, Velvac Heat/Motor/Turns STD- E-Series |
| 1 | | No Keyless Entry System Required |
| 1 | < > | Shock Absorbers, Bilstein HD Gas Charged ILOS, Front & Rear |
| 1 | | Front End Alignment, Chassis Pre-Delivery w/Printed Report |
| 1 | > | Sway Bar, Front, RoadMaster Brand |
| 1 | > | Sway Bar, Rear, RoadMaster Brand |
| 1 | < | Spare Tire |
| 1 | | Wheel Sims - Phoenix 16", Set of Four (4) Ford |
| 1 | < > | Air Fill Extensions, Rear Tires (16"), Phoenix "Air Max" |
| 1 | | AMBULANCE CONVERSION |
| 1 | | 2010 Conversion, Type III, Model 164 Commando |
| 1 | | MODULE CONSTRUCTION |
| 1 | | Roof Construction, 2x2's @ 12" o.c. (Standard) |
| 1 | | Wall Construction, 2x2's @ 12" o.c. (Type III) |

| QTY | S | DESCRIPTION |
|-----|-----|--|
| 1 | | Walk-Thru, Type III, Hinged Door w/ Fixed Plexi Window ILOS |
| 1 | < > | Bulkhead Wall Moved Forward or Rearward From Standard |
| 1 | S > | Floor Construction, Composite (No Wood) ILOS |
| 1 | | Body-to-Chassis Mounting, Type III (Standard) |
| 1 | | UNDERCOATING and INSULATION |
| 1 | | Undercoating, Underside of Module Floor (Standard) |
| 1 | | Insulation, Walls and Ceiling, 2" Fiberglass Batt (Standard) |
| 1 | | Insulation, Entry Doors, 1" Plank Foam (Standard) |
| 1 | < | Insulation, Floor, Spray Foam |
| 1 | < | Thermal Break for Ducted Heat/AC Option - (PN) |
| 1 | | EXTERIOR BODY TRIM and ACCESSORIES |
| 2 | < | Stone Guards, ADP, Front Wall (Standard) |
| 4 | | Corner Guards, Four (4) ADP w/ Corner Light Cutouts |
| 1 | > | Rub Rails, Skirt Line, One (1) Set "Premiere" Style ILOS |
| 1 | | Sill Trim, Skirt Line, One (1) Set ADP ILOS |
| 1 | | Fenderettes, One (1) Pair Stainless Steel (Standard) |
| 1 | | Fuel Fill Bezel, Cast Aluminum (Standard) |
| 1 | < | Fuel Fill Splash Guard, Brushed Stainless Steel |
| 1 | < | Drip Rail Trim Mouldings Over Door Openings (Standard) |
| 1 | < > | Rear Bumper Assembly, Kick-Up w/ Gas Struts (Std.) |
| 1 | < | Rear Bumper Flip-Up Step - Finish Rear Face w/ ADP ILOS |
| 1 | | Rear Riser, ADP (Standard) |
| 1 | | Bumper Guards, Rear, One (1) Pr. Solid Rubber, 16"w x 2.5"h |
| 1 | | License Plate Bracket, Recessed (Standard) |
| 2 | | Tow Eyes |
| 2 | | Tow Eyes Nuts |
| 2 | | Tow Eyes Box - Cast Products |
| 1 | | Tow Eyes, Rear, Chrome, One (1) Pr. in Cast Tow Eye Boxes |
| 1 | < | Mudflaps, Rear, One (1) Pair Rubber |
| 1 | | Mudflaps, Front, Included with Running Boards |
| 1 | < | Grab Bar, Exterior, One (1) Mounted Next to Side Entry Door |
| 1 | | COMPARTMENT CONSTRUCTION and COMPONENTS |
| 1 | < | Streetside-Front Compartment, ADP (Std.) |
| 1 | < | Streetside #2 Compartment, ADP (Std.) |
| 1 | | No Streetside Wheelwell Compartment Required |
| 1 | < > | Streetside-Rear Compartment, ADP (Type III Std.) |
| 1 | | ALS Compartment Door (Standard) |
| 1 | < | Compartment, Curbside, for Battery Storage |
| 1 | < | Curbside Intermediate Compartment, ADP, IATS |
| 1 | < > | Curbside-Rear Compartment, Smooth Alum., ILOS w/ Sweep-Out |
| 2 | < > | Compartment Size, Other Than Standard |
| 1 | | Side Entry Stepwell, Type III, ADP (Standard) |
| 1 | < > | Multispec Finish for Compartment(s) IATS |
| 2 | < > | L-Shape Backboard Holder |
| 1 | | Vertical Divider, Delete Standard from SS#1 |
| 1 | < | Vertical Divider, Fixed, Smooth Alum. ILOS - CS-Rear Comp't. |
| 1 | < > | MultSpec Finish for Divider(s), Two Sides IATS |
| 1 | < | Adjustable Shelf in SS#2 (Standard) |
| 1 | < | Compartment Adjustable Shelf Tracks (Standard) |
| 1 | | Slide-Out Tray, Floor Mount in Curbside Battery Compartment |
| 2 | < > | Plastic Tiles, Yellow ILO Black |
| 1 | | MODULE DOOR CONSTRUCTION and COMPONENTS |
| 7 | | Trimark , Chrome Exterior |

| TY | S | DESCRIPTION |
|----|---|--|
| 1 | | Trimark , Chrome Exterior |
| 1 | | Trimark , Chrome Exterior |
| 1 | | Trimark, Interior Locking |
| 1 | | Trimark, Interior Locking |
| 1 | | Trimark, Interior Non-Locking |
| 1 | | > Tri-Mark Exterior L-Rear Entry Door |
| 1 | | Extruded/Pan Formed Hybrid Doors (Standard) |
| 1 | | Compartment and Entry Door Latching Hardware (Standard) |
| 7 | | Compartment Door Handles, Trimark (Standard) |
| 1 | | < > Compartment Door Latch Adjustment Access Ports IATS |
| 1 | | Curbside Entry Door (Standard) |
| 1 | | Curbside Entry Door Handles, Tri-Mark |
| 1 | | Rear Entry Doors (Standard) |
| 1 | | Rear Entry Doors, Cast Grabber Door Checks (Standard) |
| 1 | | Rear Entry Door Handles, Tri-Mark |
| 1 | | Curbside Entry Door Closer - Gas Strut |
| 1 | | < > Entry Door Handle, Tri-Mark IATS |
| 1 | | < > Entry Doors, Latch Adjustment Access Ports IATS |
| 1 | | WINDOWS |
| 2 | | < WINDOW, 19" x 18" DARK TINT SLIDER |
| 2 | | WINDOW, 19" x 18" DARK TINT FIXED |
| 2 | | CLAMP RING - WINDOW 19" x 18" - 2.28" WALL |
| 2 | | CLAMP RING - WINDOW 19" x 18" - 2.28" WALL |
| 1 | | < Window, Side Entry Door, Upper |
| 2 | | < Window, Rear Entry Door, Upper |
| 1 | | MISCELLANEOUS BODY COMPONENTS |
| 1 | | INTERIOR FEATURES and COMPONENTS |
| 1 | | CEILING COMPONENTS |
| 1 | | < Grab Bar, Above Cot, 1.25" x 96" Stainless Steel (Standard) |
| 1 | | < > Grab Bar IATS, Ceiling, 1.25" x 96" Stainless Steel |
| 2 | X | < American Beauty Padding Grab Bar |
| 1 | | UPHOLSTERY |
| 1 | | < > Upholstery, Seamless Vinyl, Solid Color (Standard) |
| 1 | S | < Upholstery Color, Ash Gray & American Beauty |
| 1 | | < > Seat Cushions Attached To Seat Bases With Velcro ILOS |
| 1 | | < Padded Vinyl Trim (Standard) |
| 1 | | < > Padded Vinyl Trim - Sewn 45 Degree Corners ILOS |
| 1 | | FLOOR COVERING |
| 1 | | < Flooring, Lon Seal "Lon Plate II" (Standard) |
| 1 | | Flooring Color, "Lon Plate II", Mica #421 |
| 1 | | SILL, SCUFF and COT WHEEL PLATES |
| 1 | | < Floor Sill Plates, Brushed Stainless Steel (Standard) |
| 1 | | ATTENDANT'S SEAT |
| 1 | | < > Attendant's Seat, Automotive Style |
| 1 | | < Attendant's Seat, Wise Child Safety w/3 pt. harness Seamless |

| TY | S | DESCRIPTION |
|----|-----|--|
| 1 | | Attendant's Seat Base, Wise Swivel |
| 1 | S < | Squad Bench - Seat Base |
| 1 | | ENTRY DOOR FINISHES and COMPONENTS |
| 1 | | Entry Doors, Upper Liners, Aluminum w/ Multispec Face ILOS |
| 1 | | Entry Doors, Kick Plates, ADP (Standard) |
| 3 | | Entry Door Grab Bars, 1.25" x 12" S/S Straight Bar |
| 1 | | WALL MOUNTED GRAB BARS |
| 1 | | < > Grab Bar IATS, 1.25" x 12" Alum. w/ Rubber Inserts |
| 4 | | Latch - Swell Style for Console |
| 1 | | FRONT CONSOLE |
| 1 | < | Console, Cab, Types I and III, MultiSpec Aluminum |
| 1 | S < | Drill 2 holes in Console for Dealer Supplied Cup Holders |
| 1 | | Battery charger is included in selected inverter |
| 1 | | ELECTRICAL FEATURES and COMPONENTS |
| 1 | > | 12 Volt Electrical System, V-MUX Multi-Plex |
| 2 | < | 12 Volt Recepts, Cigarette Lighter Style |
| 2 | < | 12 Volt Recepts, Cigarette Lighter Style |
| 1 | < | Clock, Analog, Battery Operated, Trin-Tec |
| 2 | | V-Mux, Hercules node |
| 1 | | V-Mux, Vista III Display Front |
| 1 | < | V-Mux, Vista III Display Rear |
| 1 | < | V-Mux, Temperature Sensor |
| 1 | | V-Mux, Shunt Interface Module |
| 1 | | V-Mux, Capacitor for heat A/C thermostat |
| 1 | | 12 VOLT POWER COMPONENTS |
| 1 | | Idle Control, OEM Electronic Throttle (Standard) |
| 1 | | 12 Volt Load Center Location [J-Box] (Standard) |
| 1 | > | 12 Volt Elec. System, V-Mux Multi-Plex |
| 1 | < > | Warning Light Sequencer System - V-Mux |
| 1 | | Load Management System, V-Mux |
| 1 | < > | Power Locks for Module Entry Doors |
| 6 | < > | Power Locks for Compartment Doors |
| 1 | > | Remote Power Switch to Activate Cab & Module Door Locks |
| 1 | < | Driver's Control Console Gauges (V-Mux) |
| 1 | < | Door Open Indicator - V-Mux |
| 1 | < | Module Power Disconnect Switch, TST Remote (Std.) |
| 1 | < > | Battery Charger/Converter, Pre-Wire (Type III) |
| 1 | > | Anti-Theft Device, Sound Off, Ignition Override |
| 1 | | 12 Volt Recepts, Cigarette Lighter Style, Two(2) |
| 2 | | 12 Volt Recepts, Cigarette Lighter Style, One (1) |
| 1 | < | Speakers, for AM/FM Radio, One (1) Pair Ceiling Mounted |
| 1 | > | Clock, Analog, Battery Operated, Trin-Tec |
| 1 | | INTERIOR LIGHTING and COMPONENTS |
| 8 | | Dome lights, LED |
| 3 | < > | Entry Door LED Warning Lights |
| 1 | | No Additional Patient Compartment Dome Lights Required |
| 1 | | Dome lights, LED Eight (8) |
| 1 | < > | Timer, 60 Minute w/o Hold Feature |
| 1 | < > | Cabinet Lighting, Surface Mount LED |
| 1 | < | Light, Side Entry Stepwell, (1) Recessed 3.5" LED |

| QTY | S | DESCRIPTION |
|-----|-----|---|
| 1 | < > | Entry Door LED Warning Lights |
| 1 | < | Action Area Light, Liteco 12" Pulsar Fluorescent |
| 1 | | EXTERIOR LIGHTING and COMPONENTS |
| 1 | S < | Exterior Lighting Requirements - General |
| 1 | | DOT LIGHTING |
| 1 | | DOT Clearance and Marker Lighting, Type III Models |
| 1 | < | Corner Lights Feature , (4) Lower Module Corners |
| 1 | | FRONT MODULE WALL EXTERIOR LIGHTING |
| 1 | | Lightbar, Front, None Required, Wheel LED Warn. w/f |
| 1 | | Lightbar, Front, None Required |
| 1 | | CAB / CHASSIS EXTERIOR LIGHTING |
| 1 | | Warn. Light, Grille, Pass. Side, Wheel LED Warn. Ford E |
| 1 | | Warn. Light, Grille, Driver Side, Wheel LED Warn. Ford E |
| 1 | | Warn. Light, Intersection, Pass Side, Wheel LED Warn. 15° |
| 1 | | Warn. Light, Intersection, Driver Side, Wheel LED Warn. 15° |
| 1 | | REAR MODULE WALL EXTERIOR LIGHTING |
| 1 | | Lightbar, Rear, None Required, Wheel LED Warn. w/f |
| 1 | | Lightbar, Rear, None Required |
| 1 | | ARROW LIGHTBARS |
| 1 | | No Arrow Bar Required |
| 1 | | Grille Bezel, E-Series Ford, Pass. Side |
| 1 | | Grille Bezel, E-Series Ford, Driver Side |
| 1 | < > | Intersection Bezel, Polished Aluminum w/ 15° Tilt E / Pass. |
| 1 | < > | Intersection Bezel, Polished Aluminum w/ 15° Tilt E / Driv. |
| 4 | | Corner Light Bezel |
| 1 | | Warn. Light, Front Passenger Side, Wheel LED w/f |
| 1 | | Warn. Light, Front Center, Wheel LED w/f |
| 1 | | Warn. Light, Front Driver Side, Wheel LED w/f |
| 1 | | Warn. Light, Rear Passenger Side, Wheel LED w/f |
| 1 | | Scene Light, Rear Passenger Side, Wheel w/f |
| 1 | | Warn. Light, Rear Center, Wheel LED w/f |
| 1 | | Scene Light, Rear Driver Side, Wheel w/f |
| 1 | | Warn. Light, Rear Driver Side, Wheel LED w/f |
| 1 | | STOP, TAIL, TURN, AND BACKUP LIGHTING |
| 1 | < | T/B/T/BU Lights, Wheel, 4x6, LED, single turns, w/f |
| 1 | | CURBSIDE MODULE WALL EXTERIOR LIGHTING |
| 1 | | Warn. Light, CS Front, Wheel LED w/f |
| 1 | | Scene Light, CS Front, Wheel w/f |
| 1 | | Scene Light, CS Rear, Wheel w/f |
| 1 | | Warn. Light, CS Rear, Wheel LED w/f |
| 1 | | STREETSIDE MODULE WALL EXTERIOR LIGHTING |
| 1 | | Warn. Light, SS Front, Wheel LED w/f |
| 1 | | Scene Light, SS Front, Wheel w/f |
| 1 | | Scene Light, SS Rear, Wheel w/f |
| 1 | | Warn. Light, SS Rear, Wheel LED w/f |

| TY | S | DESCRIPTION |
|----|-----|--|
| 12 | X < | Whelen LED Strip Lights |
| 1 | | Whelen,3x7,Red,LED, Clear Lens,w/o flange |
| 1 | | Whelen,3x7,Red,LED, Clear Lens,w/o flange |
| 2 | | Whelen,4x6,Red,LED, Clear Lens,w/ flange |
| 2 | | Whelen,4x6,Red,LED, Clear Lens,w/ flange |
| 1 | | Whelen,4x6,Clear,LED, Clear Lens,w/ flange |
| 2 | | Whelen,4x6,Clear,LED, Clear Lens,w/ flange |
| 2 | | Whelen,4X6,Amber,Turn LED,w/ flange |
| 2 | | Whelen,4X6,Red,Brake/Tail LED,w/ flange |
| 2 | | Whelen,4X6,Clear,Backup LED,w/ flange |
| 1 | | Whelen,7x9,Red,LED, Clear Lens,w/ flange |
| 1 | | Whelen,7x9,Red,LED, Clear Lens,w/ flange |
| 1 | | Whelen,7x9,Red,LED, Clear Lens,w/ flange |
| 1 | | Whelen,7x9,Red,LED, Clear Lens,w/ flange |
| 1 | | Whelen,7x9,Red,LED, Clear Lens,w/ flange |
| 1 | | Whelen,7x9,Red,LED, Clear Lens,w/ flange |
| 2 | < | Whelen,7x9,Red,LED, Clear Lens,w/ flange |
| 1 | | Whelen,7x9,Amber,LED, Clear Lens,w/ flange |
| 1 | | Whelen,7x9,Clear LED,Scene,w/ flange |
| 1 | | Whelen,7x9,Clear LED,Scene,w/ flange |
| 1 | | Whelen,7x9,Clear LED,Scene,w/ flange |
| 1 | | Whelen,7x9,Clear LED,Scene,w/ flange |
| 2 | | Whelen,7x9,Clear LED,Scene,w/ flange |
| 2 | | Whelen,7x9,Clear LED,Scene,w/ flange |
| 1 | | Whelen,500 series TIR6 |
| 1 | | Whelen,500 series TIR6 |
| 7 | | DOT Clearance and Marker Lighting RED |
| 6 | < | DOT Clearance and Marker Lighting RED |
| 7 | | DOT Clearance and Marker Lighting AMBER |
| 6 | < | DOT Clearance and Marker Lighting AMBER |
| 2 | | Whelen, 4x6 Chrome Flange |
| 2 | | Whelen, 4x6 Chrome Flange |
| 2 | | Whelen, 4x6 Chrome Flange |
| 2 | | Whelen, 4x6 Chrome Flange |
| 2 | | Whelen, 4x6 Chrome Flange |
| 2 | | Whelen, 4x6 Chrome Flange |
| 2 | | Whelen, 4x6 Chrome Flange |
| 1 | | Whelen, 4x6 Chrome Flange |
| 2 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 2 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 2 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | < | Whelen, 7x9 Chrome Flange for Super-LED |
| 1 | | License Plate Light, LED |
| 1 | | Deutsch water proof connector |
| 1 | | Deutsch water proof connector |
| 1 | | Deutsch water proof connector |
| 1 | | Deutsch water proof connector |
| 2 | | Deutsch water proof connector |
| 2 | | Deutsch water proof connector |
| 2 | | Deutsch water proof connector |

| QTY | DESCRIPTION |
|-----|---|
| 1 | WARNING LIGHT and HEADLIGHT FLASHERS |
| 1 | Warning Light Flasher, Delete |
| 1 | STROBE POWER SUPPLIES |
| 1 | AUXILIARY LIGHTING |
| 5 | < > Compartment Lights, 4" Recessed LED ILOS |
| 1 | < Spotlight, Handheld, Optronics "BlueEye", 400,000 CP (Std.) |
| 2 | < Running Board Light, LED, (1) Pair 4" Recessed |
| 1 | REFLECTORS |
| 4 | < 1" x 4" Reflector - Red (standard) |
| 1 | AUDIBLE WARNING DEVICES |
| 1 | Refer to Chassis Section Above for Correct Siren Speakers |
| 1 | < Antenna Base, Coax, Power and Ground Wires |
| 2 | < Antenna Base, Coax, Power and Ground Wires |
| 1 | Back-up Alarm, 90 dBa (Standard) |
| 1 | Siren, Carson SA-441 "Magnum" (all consoles) |
| 1 | Siren Speakers, Ford E-Series |
| 1 | COMMUNICATION PROVISIONS AND EQUIPMENT |
| 1 | > Antenna Base, Coax, Power and Ground Wires (Standard) |
| 2 | > Antenna Base, Coax(es), Power and Ground Wires IATS |
| 1 | Back-Up Camera System - Weldon V-Mux |
| 1 | ENVIRONMENTAL SYSTEMS AND COMPONENTS |
| 2 | Exhaust Fans, 12V Blower |
| 2 | Cowl Vent - 4" Polished |
| 1 | Heat / AC Pro Air #935 12v Ducted Combo System |
| 1 | < Heat / AC Water Valve |
| 8 | Heat / AC Duct Adapters |
| 8 | Heat / AC Ducted Vents |
| 8 | Heat / AC Ducted Vent Retainers |
| 8 | Heat / AC Ducted Vent Adapter |
| 1 | Heat / AC Ducting |
| 1 | Heat / AC Plenum |
| 1 | Heat / AC Face Plate |
| 1 | Heat / AC Pad |
| 1 | S Auxiliary AC Condensor, Pro Air Roof Mount |
| 1 | < Heat / AC, Pro Air Ducted Combo System |
| 1 | Heat / AC, Combo System Installed Above Walk/Pass-Thru |
| 1 | S < > Dometic Duo Therm Cool Cat Ht Pump |
| 1 | S Auxiliary AC Condensor, Pro Air Roof Mount |
| 1 | S Thermostat, Part of the V-mux system |
| 1 | Exhaust Fans, Dual 12V Blowers (Standard) |
| 1 | 110 VOLT WIRING AND COMPONENTS |
| 3 | < Recepts, Interior 110V AC Hospital Grade Duplex |
| 1 | < Recepts, Interior 110V AC Hospital Grade Duplex |
| 1 | < 110 Volt AC Wiring And Components, Type II and III |

| TY | S | DESCRIPTION |
|----|---|---|
| 1 | | < > Shoreline, 20A Kussmaul "Super Auto-Eject" |
| 1 | | < > Shoreline, 20A Kussmaul "Super Auto-Eject" |
| 1 | | > Inverter, Pre-Wire (Standard) |
| 1 | | Refer to Part #31-20-xxxx for Specific Inverter Information |
| 1 | S | < > Dlr Supplied Install Inverter, Dimensions 1200W w/Charger |
| 1 | | Recepts, 110V AC Hospital Grade Duplexes |
| 1 | S | < > J-Box Door, Angled ILOS |
| 1 | | CABINET CONSTRUCTION |
| 1 | S | > Interior Cabinetry, Alum. Structure |
| 1 | S | Multispec Color: MS99-6075 |
| 1 | | CEILING FINISHING |
| 1 | | < Headliner, Patient Compartment, Aluminum |
| 1 | | ELECTRICAL (J-BOX) CONSTRUCTION |
| 1 | | < > Electrical (J-Box) Door, Angled ILOS |
| 1 | | ALS CABINET |
| 1 | | ALS Cabinet - Standard Configuration |
| 1 | | < Glove Box Cabinet, Three Hole Design Above Side Entry |
| 1 | | SQUAD BENCH and COMPONENTS |
| 1 | S | Squad Bench Base, Aluminum Construction (no wood) |
| 1 | | Floor Cove, 3" Recessed at Squad Bench Riser |
| 1 | S | < > Scuff Plate, Mirror S/S, Squad Bench Riser, Isle |
| 1 | S | < > Scuff Plate, Mirror S/S, Squad Bench Riser, Front End |
| 1 | | < Squad Bench Lid, Single, Aluminum |
| 1 | S | < > Trash Disposal, Recessed At Head Of Squad Bench IATS |
| 1 | S | < Safety Web At Forward End of Squad Bench to Ceiling |
| 1 | S | < > Post and Wheel Cups Installed on Squad Bench Lid |
| 1 | | No Dry Erase Writing Board Required |
| 1 | | < > Cabinet Above Squad Bench |
| 1 | | < Cabinet Above Rear Doors IATS |
| 1 | | STREETSIDE CABINERY |
| 1 | | Streetside Cabinetry - Standard Configuration |
| 1 | | < Glove Box Cabinet IATS, Three Hole Design Lower Streetside |
| 1 | S | < > Scuff Plate IATS, Mirror S/S, Lower Streetside Cabinet Wall |
| 1 | | CPR SEAT |
| 1 | | Refer to Part #14-25-xxxx for CPR Seat Construction Info. |
| 1 | | < CPR Seat w/ Hinged Backrest and Seat |
| 1 | | < > Cabinet Above CPR Seat |
| 1 | | ACTION / MONITOR-DEFIB. AREA COMPONENTS |
| 1 | | < > Countertop, Action Area, Solid Surface Material |
| 1 | | < > Countertop, Monitor/Defib, Solid Surface Material |
| 1 | | Solid Surface Countertop Color - Midnight |
| 1 | S | < > Pull-Out Drawer Under AA |
| 1 | S | < > Locking Drug Box Cabinet IATS |
| 1 | | SHELVES and SHELVING COMPONENTS |

| TY | S | DESCRIPTION |
|----|-------|---|
| 1 | < | Cabinet Shelves, .125" Aluminum |
| 1 | S < > | Cabinet Shelf Track, Unistrut Aluminum |
| 1 | | DIVIDERS |
| 1 | | CABINET DOORS and DRAWERS |
| 1 | < | Cabinet Doors, General (Korlyte) |
| 3 | < | Cabinet Door(s) Hinged Restock ILO Sliding Plexi. |
| 1 | < | Additional Cabinet Door(s) Picture Frame Korlyte |
| 1 | < > | Plexiglas Color, Clear |
| 1 | < > | Door/Drawer Latch, Southco M1 S/S - Locking |
| 1 | S < > | Door/Drawer Latch, Southco Trigger Style, Chrome, Locking |
| 1 | < > | Door/Drawer Latch, Southco Trigger Style Chrome, NonLocking |
| 1 | < | KKK Compliancy Regarding Overhead Cabinetry |
| 1 | < | KKK Compliancy Regarding Overhead Cabinetry |
| 1 | | MEDICAL SYSTEMS and COMPONENTS |
| 1 | | On-Board Cylinder Lift, ZICO for "H" Cylinder |
| 1 | < > | Electric Oxygen System |
| 1 | | Oxygen Regulator with Transducer |
| 2 | < | Oxygen Outlets, Ohio Style Quick Disconnect |
| 1 | < | Oxygen Outlets, Ohio Style Quick Disconnect |
| 2 | | Vacuum Outlet, Ohio Style |
| 2 | | Vacuum Pump, Gast |
| 2 | | IV Hangers, Cast Products Recessed in Ceiling |
| 1 | < | Sharps Container, Mail Box Style, 5-Quart |
| 1 | < | Trash Container, 2 Gallon |
| 1 | | Sharps Container Bracket 5-Quart |
| 1 | | OXYGEN SYSTEM and EQUIPMENT |
| 1 | | Oxygen System - General |
| 1 | < > | On-Board Oxygen Cylinder Lift, ZICO for "H" Cylinder ILOS |
| 1 | | Oxygen Cylinder Wrench (Standard) |
| 1 | > | Oxygen Outlets, Ohio Style Quick Disconnect |
| 1 | > | Oxygen Outlets, Ohio Style Quick Disconnect IATS |
| 1 | | Electric Oxygen System - w/V-Mux Display |
| 1 | | MEDICAL AIR SYSTEM and EQUIPMENT |
| 1 | | No On-Board Medical Air System Required |
| 1 | | VACUUM SYSTEM and EQUIPMENT |
| 2 | | Vacuum Outlet, (1) Ohio Style in Action Area (Standard) |
| 2 | < | Vacuum Pump, Gast (Standard Types I and III) |
| 2 | | Vacuum, Aspirator, RICO RS4X Disposable (Standard) |
| 1 | | IV SYSTEM and EQUIPMENT |
| 1 | | IV Hangers, Cast Products Recessed in Ceiling (Standard) |
| 1 | | BIO-WASTE CONTAINERS |
| 1 | > | Sharps Container, Mail Box Style, 5-Quart w/ Wire Bracket |
| 1 | > | Trash Container, 2 Gallon, Installed |
| 1 | | COT AND STRETCHER EQUIPMENT |

| TY S | DESCRIPTION |
|------|--|
| 1 | PRIMARY COTS |
| 1 | No Patient Cot Required |
| 1 | COT FASTENERS |
| 1 | Cot Fastener, Ferno-Washington 175-4 Dual Position |
| 1 | Cot Mounts, Set for FW Model 29 or 93 - Side and Center |
| 1 | STRETCHERS and EQUIPMENT |
| 1 | DECALS and LETTERING |
| 1 | K-SPEC LETTERING |
| 1 | < > Decals, K-Spec Lettering (Standard - Shipped Loose) |
| 1 | STAR-OF-LIFE DECALS |
| 1 | < > Decals, Star-of-Life Package (Ship Loose - Install Roof SOL) |
| 1 | CUSTOM DECALS |
| 1 | < > Decals, "Marque" Logo for Demos |
| 1 | CUSTOM LETTERING |
| 1 | DECAL STRIPING |
| 1 | PAINT |
| 1 | MODULE PAINT |
| 1 | < Paint, Module, PPG - White (Standard) |
| 1 | CHASSIS PAINT |
| 1 | PAINT STRIPING |
| 1 | Paint Stripe, Beltline, Delete (no paint stripe desired) |
| 1 | MISCELLANEOUS EQUIPMENT and COMPONENTS |
| 1 | < Stretcher Strap, Exterior Compartment (Standard) |
| 1 | < > Equipment Strap(s), Seat Belt Style IATS |
| 1 | < Interior Safety Signs (Standard) |
| 1 | < Battery Compartment Warning Sign (Standard) |
| 1 | Owner's Manual / Equipment Packet / OEM Manual |
| 1 | Fuel Surcharge |
| 1 | WARRANTIES |
| 1 | > Warranty, Ambulance Module Structure |
| 1 | > Warranty, Ambulance Conversion Electrical |
| 1 | > Warranty, Ambulance General Conversion |

